

Coherent® High Sensitivity Optical Power Sensor 1168337 | UV/VIS, 325-1065nm (USB)

See More by [Coherent®](#)



Stock **#68-625** [CONTACT US](#)

-

1

+

£1,472⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£1,472.00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	USB UV/MS Coherent Part Number: 1168337
Type:	Meterless
Calibration Uncertainty (%):	±1

Cooling Method:		Air
Physical & Mechanical Properties		
Active Area Diameter (mm):		10.0
Optical Properties		
Wavelength Range (nm):		325 - 1065
Sensor		
Type of Sensor:		Silicon
Electrical		
Maximum Incident Beam Power (mW):		100
Minimum Incident Beam Power (nW):		5000
Noise Equivalent Power NEP (nW):		100
Power Range:		10μW - 100mW
Hardware & Interface Connectivity		
Length of Cable (m):		2.5
Computer Interface:		USB
Regulatory Compliance		
RoHS 2015:		Exempt
Reach 224:		Contains SVHC(s)
Certificate of Conformance:		View

Product Details

- Utilize Silicon or Germanium Detectors
- Ideal for nW to Low mW CW Laser Measurements
- Removable Light Shield
- Compatible with [Coherent® Laser Power and Energy Meters](#)

Coherent® High Sensitivity Optical Power Sensors are semiconductor sensors designed for nanowatt to low milliwatt continuous wave laser measurements. These semiconductor sensors are available for detection from the ultraviolet to the infrared, and feature a removable light shield. An attenuator is also available that will boost power up to 5W.

Note: OP-2 sensors are compatible with the LabMax-Pro ([#35-203](#)), LabMax-TOP/TO ([#88-412](#)), FieldMaxII-TOP/TO ([#66-277](#)), and FieldMate ([#59-978](#)) meters.