

[See all 7 Products in Family](#)

## Solarization-Resistant Reflection/Backscatter Probe, Silicone-coated steel monocoil

See More by [Ocean Optics](#)



Stock #90-559 **NEW** 1 In Stock

⊖ 1 ⊕ £997<sup>80</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£997.60 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

QR400-7-SR **Model Number:**

Solarization-Resistant Reflection/Backscatter  
Probe, Silicone-coated steel monocoil **Title:**

### Physical & Mechanical Properties

400 **Core Diameter (µm):**

**Jacket Material:**  
Silicone Monocoil, PVDF Zip Tube

**Long Term Bend Radius (cm):**  
16

**Short Term Bend Radius (cm):**  
8

## Optical Properties

**Wavelength Range (nm):**  
200 - 1100

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 250:**  
[Compliant](#)

## Product Details

- Versatile Sampling for Diffuse/Specular Reflectance, Backscatter & Fluorescence
- Various Wavelength and Environmental Durability Models
- Extreme Solarization-Resistant (XSR) Probe Features Ultra-Low Loss Fiber for Harsh UV Exposure
- Connects Directly with Ocean Optics Spectrometers & Accessories

Ocean Optics Reflection/Backscatter Probes are compact, fiber-coupled sampling tools for measuring diffuse and specular reflectance, backscatter, or fluorescence in solids, solutions, or powders, and connect directly with [Ocean Optics Spectrometers and Accessories](#). They provide quantitative insights into a sample's color, appearance, and chemical composition. Choose from Visible-NIR, Solarization-Resistant, or XSR models for applications ranging from routine reflectance to demanding UV measurements. With durable jacketing, precision ferrules, and solarization-resistant fiber, the rugged design ensures reliable performance even in harsh conditions. Ocean Optics Reflection/Backscatter Probes can be optimized for UV applications, with the XSR probe featuring ultra-low loss fiber designed to withstand harsh UV exposure.