

TECHSPEC® 25.4mm Optic Dia., Thin Mirror Mount, 8-32



TECHSPEC® Compact Mirrors & Lens Mounts

Stock **#13-591** 3-4 DAYS

⊖ 1 ⊕ **£16.15**

ADD TO CART

Qty 1-4
£16.15
Qty 5+
£15.39
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Fixed

Size of Compatible Optics (mm):
25.4

Construction:
Black Anodized Aluminum

Type of Optics: Circular
Note: Available in Quick Start Kit: #17-535
Optic Holding Style: Held by One Set Screw
Clear Aperture CA (mm): 22.9
Min. Thickness of Compatible Optics (mm): 2.8
Compatible Post: 8/32
Centerline Height (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
