

TECHSPEC® 242mm Telecentric Backlight Illuminator



TECHSPEC® Telecentric Backlight Illuminators

Stock #12-229 3-4 DAYS

- 1 + **£4,377.50**

ADD TO CART

Qty 1+
£4,377.50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
271.00

Length (mm):
678.00

Type of Illumination:
Specialty

Note:
Aperture is not adjustable

Manufacturer:

Edmund Optics®	
Geometry:	Backlight
Beam Diameter (mm):	242
Mounting Flange Diameter (mm):	298.5
Light Mount Inner Diameter (mm):	8

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View
