

TECHSPEC® 3.5 OD 12.5mm Dia., NIR ND Filter



Near-IR (NIR) Neutral Density (ND) Filters

Stock **#36-262** 3-4 DAYS

⊖ 1 ⊕ **£69.70**

ADD TO CART

Qty 1-5
£69.70
Qty 6+
£55.76
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Optical Density OD (Average):
3.5

Substrate: ▢
[Fused Silica](#) (Corning 7980)

Coating: Metallic Based ND
Surface Quality: 40-20
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.10
Transmission (%): 0.03
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 700 - 1100
Clear Aperture (%): 80
Transmitted Wavefront, P-V: λ/4
Optical Density Tolerance (%): ±10
Parallelism (arcsec): <5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant