

TECHSPEC® 38.1mm Diameter Protected Silver Coated, λ/10 Mirror



Stock #39-215 [CONTACT US](#)

⊖ 1 ⊕ **£149.60**

ADD TO CART

Qty 1-5

£149.60

Qty 6+

£119.42

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
38.10 +0.00/-0.10

Surface Flatness (P-V):
λ/10

Substrate:
[Fused Silica](#) (Coming 7980)

Back Surface:
Commercial Polish

Surface Quality:
20-10

Dimensional Tolerance (mm):
+0.0/-0.10

Coating Specification:
R_{avg} >98% @ 450 - 2000nm
R_{avg} >98% @ 2000 - 10,000nm

Coating:
Protected Silver (450-10000nm)

Coating Type:
Metal

Bevel:
Protective bevel as needed

Clear Aperture (%):
90

Edges:
Ground

Parallelism (arcsec):
<180

Thickness (mm):
6.35 ±0.20

Type:
Flat Mirror

Wavelength Range (µm):
0.45 - 10

Wavelength Range (nm):
450 - 10000

Damage Threshold, Reference:
0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)
