

TECHSPEC® 6mm Inner Single Optic Mount



TECHSPEC Multi-Element Inner Single Optic Mounts

Stock **#38-745** 3-4 DAYS

⊖ 1 ⊕ **£27.71**

ADD TO CART

Qty 1-4
£27.71

Qty 5+
£26.26

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Fixed

Diameter of Compatible Optics (mm):
6.0

Construction:
Matte Black Anodized Aluminum (6061-T6)

Total Length (mm):	9.0
Thread Type:	M29 x0.75
Clear Aperture CA (mm):	5.2
Function:	Optic Mount (Fixed)
Max. Thickness of Compatible Optics (mm):	4.0
Min. Thickness of Compatible Optics (mm):	1.0
Edge Thickness of Compatible Optics (mm):	4.0

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View