

TECHSPEC® Hypercentric Lens for 2/3" Sensors



Hypercentric Lenses

Stock #86-586 3-4 DAYS



1



£2,596.75

ADD TO CART

Qty 1+

£2,596.75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
158.00

Maximum Diameter (mm):
55.9

Maximum Viewing Angle, MVA (°):
33.00

Note:
Circular Image on Max Sensor

Near Aperture, T (mm):

37.2
Type: Hypercentric Lens
Maximum Sensor Format: 2/3"
Working Distance (mm): 19.5
Mount: C-Mount
Convergence Point Distance, CPD (mm): 28.2
Depth of Field (mm): 9.5
Far Aperture, B (mm): 11.5
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View