



200 x 300mm Sheet of MaxiBlack Film, Low Outgassing Adhesive

See More by [Acktar](#)



Acktar Light Absorbent Foil



Stock **#13-488** [CONTACT US](#)



1



£198.90

ADD TO CART

Qty 1-5

£198.90

Qty 6+

£179.09

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

MaxiBlack™

Model Number: MXB-20X30-3
Operating Temperature (°C): -40 to +150
Dimensions (mm): 200 x 300
Type: Low Outgassing Adhesive
Coating Thickness (µm): 4 - 6
Foil Thickness (µm): 75
Abrasion Resistance: Moderate
Adhesive Thickness (µm): 60
Humidity Resistance: ML-C-48497A
Wavelength Range (µm): 0.3 - 5
Dimensions (cm): 20 x 30
Note: Typical Adhesive Outgassing Performance: 0.85% TML, 0% VCM per ASTM E595-77/84/90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant