


LUCID Vision Labs Phoenix™ PHX064S-MC, Sony IMX178, 6.3MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Phoenix™ Power over Ethernet (PoE) Cameras



Stock #13-701 [CONTACT US](#)

[Similar Cameras](#)

1 **£304.30**

ADD TO CART

Qty 1+

£304.30

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:

Monochrome Camera

Manufacturer:
Lucid Vision Labs

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#11-474](#)

Image Buffer:
128MB

Camera Family:
Phoenix™

Model Number:
PHX064S-MC

Imaging Sensor:
Sony IMX178

Type of Sensor:
Progressive Scan CMOS

Type of Shutter:
Rolling

Camera Sensor Format:
1/1.8"

Resolution (MegaPixels):
6.30

Pixels (H x V):
3,072 x 2,048

Pixel Size, H x V (µm):
2.40 x 2.40

Sensing Area, H x V (mm):
7.37 x 4.92

Frame Rate (fps):
19.50

Pixel Depth:
12 bit

Exposure Time:
30µs - 10s

Connector:
GigE, RJ45

Power Supply:
Power over Ethernet (PoE) or via GPIO with 12-24VDC
Power Supply

Power Consumption (W):
2.5 (External Power Supply)
3.1 (PoE)

GPIOs:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

Dimensions (mm):
24 x 24 x 27.35 (excludes connectors and lens mount)

Weight (g):
30

Mount:
C-Mount

Housing:
Partial

Interface Port Orientation:
Back Panel

Dynamic Range (dB):
71.99

Operating Temperature (°C):
-20 to +55

Storage Temperature (°C):
-30 to +60

GPIO Connector Type:
8-pin JST

Machine Vision Standard:
GigE Vision v2.0

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)

