






48351
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 31.683
GD RADIUS : 71.573
SCALE BAR : 200

REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

48351
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 289.3943 μm
DIFFRACTION LIMITED RANGE: 3.386 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

48351
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 1000.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

48351
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)