





62485INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 86.876
GD RADIUS : 129.078
SCALE BAR : 400

REFERENCE : CHIEF RAY


EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



CHROMATIC FOCAL SHIFT

62485INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 66.2736 μm
DIFFRACTION LIMITED RANGE: 7.009 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

62485INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

62485INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)