



NOTES:


- 1. ALLOWABLE OPTICAL MATERIAL:
FUSED SILICA CORNING 7980
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. SIX SIDEWALLS:
SURFACE ACCURACY: COMMERCIAL POLISH



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

	S1	S2		
SHAPE	PLANO	PLANO	EFL (AT 587.6nm)	NA
SURFACE ACCURACY AT 632.8nm	2 WAVES	2 WAVES	BFL (AT 587.6nm)	NA
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm

	
TITLE	8mm HEX LIGHT PIPE, 50mm lg
DWG NO	65836