




NOTES:

- 1. ALLOWABLE OPTICAL MATERIAL:  
FUSED SILICA CORNING 7980
- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
- 3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE
- 4. SIX SIDEWALLS:  
SURFACE ACCURACY: COMMERCIAL POLISH



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

	S1	S2		
SHAPE	PLANO	PLANO	EFL (AT 587.6nm)	NA
SURFACE ACCURACY AT 632.8nm	3 WAVES	3 WAVES	BFL (AT 587.6nm)	NA
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm

 Edmund Optics®	
TITLE	10mm HEX LIGHT PIPE, 175mm lg
DWG NO	65839