




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $t_p(\%)$	96
PASSBAND LIMIT 1 λ_{p1} (nm)	850
CUT-OFF POSITION λ_c (nm)	800±9
STOPBAND LIMIT λ_s (nm)	740
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED



TITLE	50.8 x 50.8mm, HOYA IR-80 LONGPASS FILTER
DWG NO	66070
SHEET	1 OF 1