




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



REV. A	VALUE
SHAPE	PLANO
TRANSMISSION WAVELENGTH	473 - 647.1
DURABILITY	MIL-C-48497A
CUT-ON WAVELENGTH	466
SURFACE FLATNESS	>95
SURFACE QUALITY	60-40
CLEAR APERTURE	Ø8.8
BEVEL	PROTECTIVE AS NEEDED

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**



THIRD ANGLE  
PROJECTION

TITLE

Ø12.5mm, 466nm, DICHROIC LASER BEAM  
COMBINER

ALL DIMS IN

mm

DWG NO

86383

SHEET  
1 OF 1