



NOTES:

- 1. SUBSTRATE:  
N-BK7
- 2. INCIDENT AND REFLECTED BEAMS SHALL BE PARALLEL TO WITHIN 3 ARCSEC
- 3. COATING (APPLY ACROSS COATING APERTURE)  
S1: SILVER WITH PROTECTED OVERCOAT (BLACK OVERPAINT)  
R(ABS) > 97% FROM 400 - 2500nm @ 0° AOI  
R(AVG) > 98% FROM 400 - 2500nm @ 0° AOI  
S2: NONE

4. FINE GRIND SURFACE



5. ROHS: COMPLIANT

Note: Protective Overcoat Increases diameter by 30-60µm



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV A	S1 & S2	 Edmund Optics®			
SURFACE FLATNESS	λ/8		TITLE	50.8mm SILVER COATED, CORNER CUBE PRISM	
SURFACE QUALITY	60-40		DWG NO	45191	SHEET 1 OF 1
WAVELENGTH RANGE	400 - 2200 nm				
BEVEL	PROTECTED AS NEEDED				
		ALL DIMS IN	mm		