





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	488nm
FULL WIDTH HALF MAX (FWHM)	3 ±1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	350 - 483 & 553 - 650nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

Ø25mm, 488nm CWL, 3nm FWHM, HARD COATED LASER CLEAN-UP FILTER

DWG NO

68872

SHEET

1 OF 1