NOTES:

- 1. SUBSTRATE MATERIAL: N-BK7
- 2. BEAM DEVIATION: ±3 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1, \$2, \$3 & \$4: R(abs) <0.25% @ 532nm \$5: Tp/Ts >1000:1 @ 532nm TRANSMISSION >95% REFLECTION >99.5%



FINE GROUND SURFACE




 $\sqrt{5}$. ELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE 61

6. PROTECTIVE BEVEL AS NEEDED



MARK IDENTIFIES BEAMSPLITTER COATING RIGHT ANGLE PRISM



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			_			Edmund Opt	ICS ®
	\$1, \$2, \$3, \$4	\$5			W		163
SHAPE	PLANO	PLANO				10mm, 532nm, LASER LINE POLARIZI	NG CLIRE
SURFACE FLATNESS	λ/4	λ/4	THIRD ANGLE PROJECTION		TITLE	BEAMSPLITTER	
SURFACE QUALITY	40-20	40-20		1		52	CUEET
CLEAR APERTURE	90	90	ALL DIMS IN	mm	DWG NO	48571	SHEET 1 OF 1