

NOTES:



1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Gold (700-10000nm)

R(AVG) >96% @ 700 - 2000nm

R(AVG) >96% @ 2000 - 10,000nm



S2: NONE
3. EDGES SEAMED
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	N/A
SURFACE FLATNESS	4 - 6λ	N/A
CLEAR APERTURE	5.00 x 7.50	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 		 Edmund Optics®	
TITLE		6 x 8.5mm Protected Gold, 4-6λ Mirror	
ALL DIMS IN	mm	DWG NO	43878
			SHEET 1 OF 1