



NOTES:

1. SUBSTRATE MATERIAL: N-BK7
2. BEAM DEVIATION:  $\pm 5$  ARCMIN
3. ROHS COMPLIANT
4. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1 & S2: R(avg) >85% @ 400 - 700nm W/BLACK OVERPAINT
  - S3 & S4: R(avg)  $\leq 0.4\%$  @ 425 - 675nm
  - S5: BLACK PAINT

 FINE GRIND SURFACE


FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
ANGLE TOL.	$\pm 5$ arcmin
SURFACE QUALITY	60-40
SURFACE FLATNESS	$\lambda/8$
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

20mm, VIS 0° COATED, PENTA PRISM

DWG NO

48598

SHEET  
1 OF 1