



NOTES:


1. SUBSTRATE: POLYMER FILM XP42-75
2. OPERATING TEMPERATURE: -40 TO +80 °C
3. WAVELENGTH RANGE: 400 - 700 nm
4. POLARIZATION: >99
5. TRANSMISSION (%):  
 Single: 42  
 Parallel: 36  
 Crossed: <0.004
6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                                                                                                              |    |        |                                                    |              |
|--------------------------------------------------------------------------------------------------------------|----|--------|----------------------------------------------------|--------------|
| THIRD ANGLE PROJECTION  |    | TITLE  | 200.0 x 200.0mm, 0.75mm, POLARIZING LAMINATED FILM |              |
| ALL DIMS IN                                                                                                  | mm | DWG NO | 86189                                              | SHEET 1 OF 1 |