



NOTES:

- 1. SUBSTRATE : FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: ALUMINIZED
 - R(avg) >85% @ 400 - 700nm W/BLACK OVERPAINT
 - 0.3 J/cm² @ 532 & 1064nm, 10ns
 - S2: UV-VIS
 - R(avg) ≤1.5% @ 250 - 700nm
 - R(abs) ≤1.0% @ 350 - 450nm
 - 3 J/cm² @ 355nm, 10ns
 - 5 J/cm² @ 532nm, 10ns

3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
ANGLE TOLERANCE (arcsec)	±40	±40				
PYRAMID TOLERANCE (arcmin)	±1	±1				
SURFACE QUALITY	20-10	20-10				
SURFACE FLATNESS	λ/10	λ/10				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				

THIRD ANGLE PROJECTION		TITLE	5mm ALUMINUM & UV-VIS, FUSED SILICA HIGH TOLERANCE RA PRISM		
ALL DIMS IN	mm	DWG NO	47800	SHEET 1 OF 1	

Edmund Optics®