

NOTES:



1. SUBSTRATE MATERIAL:
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS-NIR (400-1000nm)
R(ABS) ≤0.25% @ 880nm
R(AVG) ≤1.25% @ 400 - 870nm
R(AVG) ≤1.25% @ 890 - 1000nm


3. FINE GROUND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	150.00	 Edmund Optics®	25mm DIA X 150mm FL VIS-NIR COATED, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	147.7			
RADIUS	77.78	INFINITY	THIRD ANGLE PROJECTION 	TITLE	25mm DIA X 150mm FL VIS-NIR COATED, CYLINDER LENS		
SURFACE QUALITY	60-40	60-40		DWG NO			
CLEAR APERTURE	Ø24.00	Ø24.00	ALL DIMS IN	mm			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					