

NOTES:

1. SUBSTRATE MATERIAL:
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS-NIR

R(abs) ≤0.25% @ 880nm



R(avg) ≤1.25% @ 400 - 870nm

R(avg) ≤1.25% @ 890 - 1000nm

3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL	20		Edmund Optics® 10mm DIA X 20mm FL VIS-NIR COATED, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	18.03			
RADIUS	10.34	∞	THIRD ANGLE PROJECTION		TITLE		
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO		
CLEAR APERTURE	Ø9.00	Ø9.00					SHEET 1 OF 1
COATING APERTURE	Ø9.00	Ø9.00					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					