NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: 50% R ±5% @ 550nm 50% T ±5% @ 550nm

S2: AR ¹/₄λ MgF2 @ 550nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	REV. A	\$1	\$2	
	SHAPE	PLANO	PLANO	
	SURFACE QUALITY	80-50	80-50	
	SURFACE FLATNESS	4 - 6λ	4 - 6λ	
	BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	
	·			

THIRD ANGLE PROJECTION	\oplus	TIT
ALL DIMS IN	mm	DV

B	Edmund Optics ®
TLE	60 x 85mm, 50 R/50 T, PLATE BEAMSPLITTER

l dims in	mm	DWG NO	64408	SHEET