



NOTES:

- 1. SUBSTRATE MATERIAL:
N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0°


R(avg) ≤0.4% @ 425 - 675nm

- 3. FINE GROUND SURFACE
- 4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
- 5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2							
SHAPE	CONVEX	PLANO	EFL	-50	 Edmund Optics®				
RADIUS	-25.84	∞	BFL	-51.32					
SURFACE QUALITY	60-40	60-40			TITLE	12.5mm DIA X -50mm FL VIS 0° COATED, CYLINDER LENS			
CLEAR APERTURE	Ø11.50	Ø11.50							
COATING APERTURE	Ø11.50	Ø11.50							
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	69795		SHEET 1 OF 1	