

## NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO < 1ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) S1 & S2: R(ABS) ≤0.25% @ 880nm R(AVG) ≤1.25% @ 400 - 870nm R(AVG) ≤1.25% @ 890 - 1000nm



5. Rohs Compliant







## PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	60-40	60-40	
CLEAR APERTURE	Ø22.50	Ø22.50	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

THIRD ANGLE PROJECTION	$\phi$	TITLE
ALL DIMS IN	mm	DWG NO

Edmund Optics®
 25mm DIA., 1mm THICK, VIS-NIR COATED λ/4

1 OF 1

$\bigoplus$	TITLE	N-BK7 WINDOW	J
mm	DWG NO	2/007	SHEET

36997