
NOTES:


- SUBSTRATE: UV GRADE FUSED SILICA 1.
- 2. COATING (APPLY ACROSS COATING APERTURE) S1 & S2: RAVG ≤0.4% @ 425 - 675nm
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN <5 ARCSEC

<u>/4.\</u>

FINE GRIND SURFACE

5. **ROHS COMPLIANT**





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	20-10	20-10	
CLEAR APERTURE	Ø60.00	Ø60.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

			Edmund Optic	S®
HIRD ANGLE ROJECTION	\$	TITLE	75mm DIA., 3mm THICK, VIS 0° COATED FUSED SILICA WINDOW	λ/10
all DIMS IN	mm	DWG NO	36960	SHEET 1 OF 1