


NOTES:

- 1. COATING (APPLY ACROSS COATING APERTURE)
T(AVG): >80% FROM 400 - 480
CUT-OFF WAVELENGTH: 500nm ± 3%
BLOCKING RANGE: 520 - 615nm
- 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

	S1	S2	THIRD ANGLE PROJECTION		TITLE	500nm, 12.5mm Square, OD 2 Ultra-Thin Shortpass Filter	
SHAPE	PLANO	PLANO					
CLEAR APERTURE	11.25 x 11.25	11.25 x 11.25	ALL DIMS IN		DWG NO	35892	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1	