



NOTES:


1. COATING:  
S1: SPECTRAL BLACK™  
THICKNESS (µm) 3-7
2. ABSORBANCE: 99.9 (0 - 10° AOI)%
3. ABRASION RESISTANCE: MODERATE
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE (°C): -40 to 150
6. WAVELENGTH RANGE: 0.3 - 14
7. TYPICAL ADHESIVE OUTGASSING PERFORMANCE:  
0.85% TML  
0% VCM  
PER ASTM E595-77/84/90



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® **Edmund Optics**®

THIRD ANGLE PROJECTION 		TITLE	Spectral Black Low Outgassing Adhesive Foil Sheet 200 x 600mm	
ALL DIMS IN	mm	DWG NO	12518	SHEET 1 OF 1