## NOTES:

1. SUBSTRATE MATERIAL: Float Glass

2. COATING (APPLY ACROSS CLEAR APERTURE, SPECIFICATION APPLIES AFTER SANDBLASTING):


S1: R(AVG) >95% @ 450 - 650nm


S2: NONE



FINE GRIND SURFACE

Rohs: Compliant





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

		Edmund Optics®

	\$1	S1 S2			TITLE	12.5mm Dia. Enhanced Aluminum Coated, Reflective Diffuser	
MIN CLEAR APERTURE	Ø11.50	N/A		mm	DWG NO	SHEET SHEET	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN			12451	1 OF 1