




NOTES:

- 1. SUBSTRATE:  
Fused Silica
- 2. COATING (APPLY ACROSS COATING APERTURE):  
S1 & S2: NONE
- 3. EFFECTIVE FOCAL LENGTH: 13.80 mm
- 4. DIVERGENCE ANGLE:  $\pm 1.2^\circ$
- 5. WAVELENGTH RANGE (nm): 200 - 2200
- 6. ROHS: COMPLIANT




DETAIL A



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                                                                                                              |    |        |                                                         |              |
|--------------------------------------------------------------------------------------------------------------|----|--------|---------------------------------------------------------|--------------|
| THIRD ANGLE PROJECTION  |    | TITLE  | Microlens Array 10 x 10mm, 500µm Pitch, 1.2° Divergence |              |
| ALL DIMS IN                                                                                                  | mm | DWG NO | 64479                                                   | SHEET 1 OF 1 |