NOTES:

1. MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 350 - 600nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

INFORMATION ONLY: Sto All to A line to the last only in the state of the last only in the

	THIRD ANGLE _ PROJECTION	$\phi \Box$	TITLE	543nm Alignment, 0.40 NA Fiber Collim FC Connector	ator w/
PARTS TO THIS DRAWING	ALL DIMS IN	mm	DWG NO	64769	SHEET 1 OF 1