



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATION	VALUE
CENTER WAVELENGTH (CWL)	350nm ± 5 nm
FULL WIDTH HALF MAX (FWHM)	50nm ± 5 nm
MINIMUM TRANSMISSION	>90 %
BLOCKING	≥ 4.0 FROM 200 - 1200 nm
SURFACE QUALITY	80-50
CONSTRUCTION	MOUNTED IN BLACK ANODIZED ALUMINUM RING
COATING TYPE	Hard Coated

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]



ALL DIMS IN

mm

TITLE

350nm CWL, 50mm Dia. Hard Coated OD 4
50nm Bandpass Filter

DWG NO

12099

SHEET
1 OF 1