



PART	PART #	MATERIAL
①	#48-530	Hoya ND-0.3
②	#55-246	Anodized Aluminum

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	FILTER SPECIFICATIONS
CLEAR APERTURE (mm)	> $\varnothing 11.00$
TRANSMISSION	T (AVG) > 3% @ 400 - 700 nm
OPTICAL DENSITY	1.5 \pm 0.1
SURFACE QUALITY	80-50

<div> <div> <div></div> <div></div> </div> <div> <div></div> <div></div> </div> </div> <div>Edmund Optics®</div>			
<div> <div>THIRD ANGLE PROJECTION</div> <div></div> </div>		<div>TITLE</div> <div>1.5 OD, 12mm CA, C-Mount Absorptive ND Filter</div>	
<div>ALL DIMS IN</div> <div>mm</div>	<div>DWG NO</div> <div>12940</div>	<div>SHEET</div> <div>1 OF 1</div>	