
NOTES:


1. SUBSTRATE: N-BK7

- 2. S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) <0.25% @ 532nm R(ABS) <0.25% @ 1064nm R(AVG) <1.0% @ 500 - 1100nm



5. Rohs Compliant





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø45.00	Ø45.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			Edmund Optics ®			
	THIRD ANGLE PROJECTION		TITLE	50mm DIA., 6mm THICK, YAG-BBAR COATED, λ/4 N-BK7 WINDOW		
D	ALL DIMS IN	mm	DWG NO	13328	SHEET 1 OF 1	

