

NOTES:


1. SUBSTRATE:
S-LAH64
2. CENTERING TOLERANCE (AT 587.6nm):
BEAM DEVIATION (HALF ANGLE): <3 arcmin
3. COATING (APPLY ACROSS COATING APERTURE)
S1: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI
S2: VIS (350-700nm)
Ravg < 0.5% @ 350 - 700nm @ ±30° AOI
Rabs < 1.5% @ 350 - 700nm @ ±30° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 Y^2}{1 + \sqrt{1 - (1+k) (\frac{1}{RADIUS})^2 Y^2}} + D*Y^2 + E*Y^4 + F*Y^6 + G*Y^8 + H*Y^{10} + J*Y^{12} + L*Y^{14}$$



SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	2.250000E+01
(1/RADIUS)	4.02252615E-02
k	-7.100000E-01
D	0.000000E+00
E	6.645300E-07
F	-7.47800E-10
G	-8.533600E-13
H	-4.328100E-16
J	3.380900E-19
L	0.000000E+00

	S1	S2				
SHAPE	CONVEX	PLANO	BFL @ 780nm: 24.18			
RADIUS	24.860	INFINITY				
SURFACE QUALITY	40-20	40-20				
CLEAR APERTURE	40.5 mm	40.5 mm				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			THIRD ANGLE PROJECTION		TITLE	45mm Dia., 0.70 NA, 350-700nm Coated, NIR Aspheric Lens
			ALL DIMS IN	mm	DWG NO	16275
						SHEET 1 OF 1

Edmund Optics®

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY