



- NOTES:
- 1. SUBSTRATE: N-BK7
 - 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1&S2: R(ABS) ≤1.5% @ 750 - 800nm
 - R(ABS) ≤1.0% @ 800 - 1550nm
 - R(ABS) ≤0.7% @ 750 - 1550nm

4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT
- 6. TRANSMITTED WAVEFRONT (P-V):
λ/4 (per inch over clear aperture)



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		S1	S2				Edmund Optics®	
SHAPE		PLANO	PLANO	THIRD ANGLE PROJECTION			TITLE	25mm Sq., 1mm Thick, NIR II Coated λ/4 N-BK7 Window
SURFACE QUALITY		60 - 40	60 - 40					
CLEAR APERTURE		Ø 22.50 x 22.50	Ø 22.50 x 22.50					
BEVEL		PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	25802	SHEET 11 OF 14