


NOTES:

1. SUBSTRATE:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: SILVER OVERCOATED WITH INCONEL & BLACK PAINT
R(ABS) >87% FROM 450 - 500nm @ 45° AOI
R(ABS) >94% FROM 500 - 2000nm @ 45° AOI
R(AVG) >96% FROM 400 - 2500nm @ 45° AOI
- S2: NONE

3. FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	19.08 x 13.00	19.08 x 13.00
COATING APERTURE	19.08 x 13.00	19.08 x 13.00
SURFACE FLATNESS	$\lambda/4$	$\lambda/4$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	15mm Silver Coated, N-BK7 Right Angle Prism
mm		DWG NO	26748
		SHEET 5 OF 10	