



NOTES:


- 1. COATING:
S1: MAXIBLACK™
THICKNESS: 4 - 6 (µm)
- 2. ABSORBANCE: 98%
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 TO +150
- 6. WAVELENGTH RANGE (µm): 0.3 - 5



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

<div><div>EO[®]</div><div>Edmund Optics[®]</div></div>			
THIRD ANGLE PROJECTION 		TITLE	10 x 10cm Sheet of MaxiBlack Film, Low Outgassing Adhesive
ALL DIMS IN	mm	DWG NO	28945
			SHEET 1 OF 1