

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Achromatic Lenses](#)

## Ultra-Broadband Achromatic Lenses



- Broadband Color-Corrected Design
- >90% Transmission from 800 to 4000nm
- Ideal for Hyperspectral Imaging Applications
- [Near-IR \(NIR\) Achromatic Lenses](#) Also Available

**Technical Information**

## Products

| EFL<br>(mm) | Coating                  | Housing<br>Diameter<br>(mm) | Construction                    | Transmitted<br>Wavefront<br>Error, RMS | Stock<br>Number         | Price                                     | Buy        |
|-------------|--------------------------|-----------------------------|---------------------------------|----------------------------------------|-------------------------|-------------------------------------------|------------|
| 100.00      | BBAR<br>(800-<br>4000nm) | 30.48                       | Anodized<br>Aluminum<br>Housing | < $\lambda/2$ @<br>633nm               | <a href="#">#16-046</a> | £812.00<br><a href="#">Volume Pricing</a> | 1 In Stock |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK  
Phone: 1-800-363-1992 :  
[www.edmundoptics.com](http://www.edmundoptics.com)