

[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Infrared](#)

ISP Optics Silicon (Si) Aspheric Lenses

 See More by [ISP Optics](#)


- Transmission from 1.2 - 7 μ m
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5 μ m

Common Specifications

Physical & Mechanical Properties

Diameter (mm):	25.40 +0.00/-0.13	Centering, ETD (μm):	<20
Clear Aperture CA (mm):	22.86	Bevel:	Protective as needed
Shape of Back Surface:	Concave	Surface Roughness ($\text{\AA}$):	<100 Ra

Optical Properties

Substrate:	Silicon (Si)	Surface Quality:	60-40
Conjugate Distance:	Infinite	Irregularity (P-V) @ 632.8nm:	$\lambda/4$

Technical Information

Products

Dia. (mm)	EFL (mm)	NA	Coating	Model Number	Stock Number	Price	Buy
25.40	12.70	1.00	Uncoated	ASPH-SI- 25-12	#24-881	£455.26	5 In Stock
#24-882 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
25.40	25.40	0.50	Uncoated	ASPH-SI- 25-25		£287.12	3 In Stock

[#24-885 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive up
to 80% off
select
products.

25.40	25.40	0.50	BBAR (3000- 5000nm)	HDAR35- ASPH-SI- 25-25	£384.30	5 In Stock
-------	-------	------	---------------------------	------------------------------	---------	------------

[#24-883 Clearance](#)



Clearance

Availability
is limited,
so buy
before
these
products
disappear.
Sorry, we
cannot
accept
returns.
Receive up
to 80% off
select
products.

25.40	50.80	0.25	Uncoated	ASPH-SI- 25-50	£287.12	5 In Stock
-------	-------	------	----------	-------------------	---------	------------



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com