

[All Products](#) / [Optics](#) / [Fiber Optics](#)

High Power Multimode Fiber Optic Patchcords



- Low-OH Silica Core, 0.22 Numerical Aperture (NA)
- SMA Connector and Standardized 2m Length
- 380 – 2200 Wavelength Range

Common Specifications

Physical & Mechanical Properties

Length (m):	2.00	Jacket Material:	Stainless Steel
Jacket Diameter (mm):	6.35		

Optical Properties

Numerical Aperture NA:	0.22 0.02
Wavelength Range (nm):	380 - 2200

Hardware & Interface Connectivity

Connector:	SMA
------------	-----

Technical Information

Products

Title	Stock Number	Price	Buy
200µm Low-OH Silica Core, 0.22 NA, High Power SMA Patch Cable, 2m	#72-226	£153.00	Contact Us
400µm Low-OH Silica Core, 0.22 NA, High Power SMA Patch Cable, 2m	#72-227	£174.25	Contact Us
600µm Low-OH Silica Core, 0.22 NA, High Power SMA Patch Cable, 2m	#72-228	£195.50	3 In Stock
800µm Low-OH Silica Core, 0.22 NA, High Power SMA Patch Cable, 2m	#72-229	£238.00	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com