

[See all 75 Products in Family](#)

LightPath 354850 | 6.33mm Dia., 0.13 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-544** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £68⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£68.00 each
Qty 11-49	£61.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: BK7

Compatible Window:

354850

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
6.33 ±0.015

Clear Aperture CA (mm):
5.5

Edge Thickness ET (mm):
2.35

Center Thickness CT (mm):
2.66 ±0.05

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
19.157

Optical Properties

Effective Focal Length EFL (mm):
22.00 @670nm

Numerical Aperture NA:
0.13

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
670

Coating:
BBAR (600-1050nm)

Coating Specification:
R_{abs} <1.0% @ 600 - 1050nm

Surface Quality:
40-20

f#:
3.85

Abbe Number (v_d):
60.88

Index of Refraction (n_d):
1.586

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
20.41

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
670.00

Transmitted Wavefront Error (λ, RMS):
< 0.12

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
7.6

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam

shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information

