

[See all 75 Products in Family](#)

LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-100** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £68.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£68.00 each
Qty 11-49	£61.20 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: BK7

Compatible Window:

354260

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):

6.50 ±0.015

Clear Aperture CA (mm):

5

Edge Thickness ET (mm):

1.8

Center Thickness CT (mm):

2.21 ±0.05

Bevel:

Protective as needed

Distance from Window to Lens (D) (mm):

12.727

Optical Properties

Effective Focal Length EFL (mm):

15.29 @ 780nm

Numerical Aperture NA:

0.16

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

780

Coating:

BBAR (1050-1600nm)

Coating Specification:

R_{abs} <1.0% @ 1050 - 1600nm

Surface Quality:

40-20

f#:

3.12

Abbe Number (v_d):

50.22

Index of Refraction (n_d):

1.586

Wavelength Range (nm):

1050 - 1600

Working Distance (mm):

13.98

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

780.00

Transmitted Wavefront Error (λ, RMS):

< 0.09

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.6

Environmental & Durability Factors

Operating Temperature (°C):

≤200

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures


LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam

shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

Technical Information



Compatible Mounts