

[See all 14 Products in Family](#)

LightPath 354059 | 6.33mm Dia., 0.19 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Stock #83-693 **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £68.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£68.00 each
Qty 11-49	£61.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

354059 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

6.33 ±0.015

Clear Aperture CA (mm):

5.20

Edge Thickness ET (mm):

1.73

Center Thickness CT (mm):

2.35 ±0.05

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

14.00 @633nm

Numerical Aperture NA:

0.19

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

633

Coating:

BBAR (350-700nm)

Coating Specification:

$R_{avg} \leq 0.5\%$ @ 350 - 700nm

Surface Quality:

60-40

f#:

2.63

Abbe Number (v_d):

61.16

Index of Refraction (n_d):

1.589

Wavelength Range (nm):

350 - 700

Working Distance (mm):

12.600

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

633.00

Transmitted Wavefront Error (λ , RMS):

< 0.145

Material Properties

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):

7.6

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Product Details

- Compact, Molded Aspheric Lens Design
- Improved Performance Compared to Doublet and Triplet Lenses
- Ideal for Laser Tools and Measurement Systems

LightPath® Laser Tool Molded Aspheric Lenses are designed to fulfill the needs of a variety of tools and measurement systems utilizing laser diodes, including leveling lasers, projectors, scanners, trackers, and gun sights. By utilizing a single aspheric lens, the need for a multi-lens system is eliminated, allowing for a more compact and robust design. Each aspheric lens is offered with various anti-reflection coatings for optimum transmission in the visible and NIR wavelength ranges. LightPath® Laser Tool Molded Aspheric Lenses' anti-reflection coating options for each lens provides <1% average reflection over the entire design wavelength range. The lenses are offered in four different diameters: 3mm, 4.70mm, 6mm, and 6.33mm.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

