

[See all 76 Products in Family](#)

LightPath 355397 | 7.2mm Dia., 0.30 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-122** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

£60⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£60.00 each
Qty 11-49	£54.00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads


General	
Thickness: 0.28 (t) (mm) Material: BK7	Compatible Window:
355397	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications:	
Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	
7.20 ±0.020	
Clear Aperture CA (mm):	
6.68	
Edge Thickness ET (mm):	
1.28	
Center Thickness CT (mm):	
1.95 ±0.05	
Bevel:	
Protective as needed	
Distance from Window to Lens (D) (mm):	
9.346	
Optical Properties	
Effective Focal Length EFL (mm):	
11.00 @670nm	
Numerical Aperture NA:	
0.3	
Substrate: ☐	
D-ZLaF52LA	
Focal Length Tolerance (%):	
±1	
Aspheric Design Wavelength (nm):	
670	
Coating:	
BBAR (600-1050nm)	
Coating Specification:	
R _{abs} <1.0% @600 - 1050nm	
Surface Quality:	
60-40	
f/#:	
1.67	
Wavelength Range (nm):	
600 - 1050	
Working Distance (mm):	
10	
Conjugate Distance:	
Infinite	
Transmitted Wavefront Error (λ, RMS):	
< 0.09	
Environmental & Durability Factors	
Operating Temperature (°C):	
≤200	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;