

[See all 74 Products in Family](#)

LightPath 355375 | 6.51mm Dia., 0.30 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-130** [CONTACT US](#)

[Other Coating Options](#)

- 1 + £60⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | £60.00 each |
| Qty 11-49 | £54.00 each |
| Need More? | Request Quote |

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Thickness: 0.250 (t) (mm)
Material: BK7

Compatible Window:

355375

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
6.51 ±0.020

Clear Aperture CA (mm):
4.54

Edge Thickness ET (mm):
2.71

Center Thickness CT (mm):
3.19 ±0.04

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
5.151

Optical Properties

Effective Focal Length EFL (mm):
7.50 @ 780nm

Numerical Aperture NA:
0.30

Substrate:
[D-ZLaF52LA](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
780

Coating:
BBAR (600-1050nm)

Coating Specification:
R_{abs} <1.0% @ 600 - 1050nm

Surface Quality:
40-20

f#:
1.67

Abbe Number (v_d):
40.79

Index of Refraction (n_d):
1.806

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
5.8

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
780.00

Transmitted Wavefront Error (λ, RMS):
< 0.05

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
6.9

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)


Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

