

[See all 37 Products in Family](#)

0.5" Dia f/10 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock #48-169 **CLEARANCE** 14 In Stock

− 1 + £45⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£45.60 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

12.70 ±0.1 **Diameter (mm):**

Clear Aperture CA (mm):

11.4

2.0±0.1 **Edge Thickness ET (mm):**

2.30 **Center Thickness CT (mm):**

62.23 **Radius R (mm):**

Optical Properties

127.00 @ 632.8nm **Effective Focal Length EFL (mm):**

0.05 **Numerical Aperture NA:**

125.5 **Back Focal Length BFL (mm):**

PMMA **Substrate:** □

±1 **Focal Length Tolerance (%):**

632.8 **Aspheric Design Wavelength (nm):**

Uncoated **Coating:**

10.0 **f#:**

61.4 **Abbe Number (v_d):**

1.49 **Index of Refraction (n_d):**

400 - 1100 **Wavelength Range (nm):**

632.8 **Focal Length Specification Wavelength (nm):**

Environmental & Durability Factors

80.0 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 242:**

Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

;